

# P2-08ADS-2 Cut Sheet



Productivity2000 analog input module, 8-channel, voltage, 16-bit, isolated, external 24 VDC required. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-08ADS-2>

## Technical Specifications

<b>Brand</b>	Productivity2000
<b>Item</b>	Input module
<b>I/O Module Type</b>	Analog
<b>Number Of Input Channels</b>	8
<b>Input Signal Type(s)</b>	Voltage
<b>Number of Isolated Commons</b>	4
<b>Isolated Channels</b>	Yes
<b>Input Resolution</b>	16-bit

<b>Input Voltage Signal Range</b>	0-10 VDC
<b>Display Type</b>	4 x 10 character OLED display
<b>External Power Requirement</b>	24 VDC
<b>Requires</b>	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
<b>Programming Software</b>	Productivity Suite programming software v4.7 or later

## Agency Approvals

<b>UL Listed File #</b>	E139594
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/P2-08ADS-2.pdf>  
See store item page for other formats.