

P2-08TD1P Cut Sheet



Productivity2000 discrete output module, 8-point, 12-24 VDC, sinking, 1 common(s), 8 point(s) per common, 0.25A/point, short circuit and overload protection. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-08TD1P>

Technical Specifications

Brand	Productivity2000
Item	Output module
I/O Module Type	Discrete
Number of Output Points	8
Nominal Output Voltage	12-24 VDC
Discrete Output Type	Sinking
Number of Non-Isolated Output Commons	1
Number of Points per Common	8
Load Current	0.25A/point
Protection Type(s)	<ul style="list-style-type: none">• short circuit• overload
External Power Requirement	24 VDC
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v2.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document