

# P2-15CDD1 Cut Sheet



Productivity2000 discrete combo module, Input: 8-point, 12-24 VDC, sinking/sourcing, Output: 7-point, 3.3-24 VDC, sinking, 1A/point @ 60 °C, 2A/point @ 55 °C. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-15CDD1>

## Technical Specifications

<b>Brand</b>	Productivity2000
<b>Item</b>	Combo module
<b>I/O Module Type</b>	Discrete
<b>Number of Input Points</b>	8
<b>Nominal Input Voltage</b>	12-24 VDC
<b>Discrete Input Type</b>	Sinking/sourcing
<b>Number of Non-Isolated Discrete Input Commons</b>	1
<b>Number of Points per Discrete Input Common</b>	8
<b>Number of Output Points</b>	7
<b>Nominal Output Voltage</b>	3.3-24 VDC

<b>Discrete Output Type</b>	Sinking
<b>Number of Non-Isolated Discrete Output Commons</b>	1
<b>Number of Points per Discrete Output Common</b>	7
<b>Load Current</b>	1A/point @ 60 °C, 2A/point @ 55 °C
<b>Fuse Type</b>	External fusing 8A max (user supplied)
<b>External Power Requirement</b>	12-24 VDC
<b>Requires</b>	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
<b>Programming Software</b>	Productivity Suite programming software v4.7 or later

## Agency Approvals

<b>UL Listed File #</b>	E139594
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/P2-15CDD1.pdf>  
See store item page for other formats.