

P2-15CDD2 Cut Sheet



Productivity2000 discrete combo module, Input: 8-point, 12-24 VDC, sinking/sourcing, Output: 7-point, 12-24 VDC, sourcing, 1A/point @ 60 °C, 2A/point @ 55 °C. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-15CDD2>

Technical Specifications

Brand	Productivity2000
Item	Combo module
I/O Module Type	Discrete
Number of Input Points	8
Nominal Input Voltage	12-24 VDC
Discrete Input Type	Sinking/sourcing
Number of Non-Isolated Discrete Input Commons	1
Number of Points per Discrete Input Common	8
Number of Output Points	7
Nominal Output Voltage	12-24 VDC

Discrete Output Type	Sourcing
Number of Non-Isolated Discrete Output Commons	1
Number of Points per Discrete Output Common	7
Load Current	1A/point @ 60 °C, 2A/point @ 55 °C
Fuse Type	External fusing 8A max (user supplied)
External Power Requirement	12-24 VDC
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v4.7 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/P2-15CDD2.pdf>
See store item page for other formats.