

P2-16AD-2 Cut Sheet



Productivity2000 analog input module, 16-channel, voltage, 16-bit, input voltage signal range(s) of 0-10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-16AD-2>

Technical Specifications

Brand	Productivity2000
Item	Input module
I/O Module Type	Analog
Number Of Input Channels	16
Input Signal Type(s)	Voltage
Isolated Channels	No
Number of Non-Isolated Input Commons	4
Input Resolution	16-bit
Input Voltage Signal Range	0-10 VDC
Display Type	4 x 10 character OLED display
External Power Requirement	24 VDC
Requires	ZIPLink connector modules and pre-wired cables
Programming Software	Productivity Suite programming software v2.0 or later
Additional Information	No terminal block sold for this module

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document