

P2-16DA-1 Cut Sheet



Productivity2000 analog output module, 16-channel, current, 16-bit, external 24 VDC required. Requires ZIPLink connector modules and pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-16DA-1>

Technical Specifications

Brand	Productivity2000
Item	Output module
I/O Module Type	Analog
Number Of Output Channels	16
Output Signal Type	Current
Analog Output Type	Sourcing
Isolated Channels	No
Number of Non-Isolated Output Commons	2

Output Resolution	16-bit
Output Current Signal Range	4-20 mA
Display Type	4 x 10 character OLED display
External Power Requirement	24 VDC
Requires	ZIPLink connector modules and pre-wired cables
Programming Software	Productivity Suite programming software v2.0 or later
Additional Information	No terminal block sold for this module

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/P2-16DA-1.pdf>
See store item page for other formats.