

P2-16ND-TTL Cut Sheet



Productivity2000 discrete input module, 16-point, 3.3-5 VDC, sinking/sourcing/TTL, 2 common(s), 8 point(s) per common. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-16ND-TTL>

Technical Specifications

Brand	Productivity2000
Item	Input module
I/O Module Type	Discrete
Number of Input Points	16
Nominal Input Voltage	3.3-5 VDC
Discrete Input Type	Sinking/sourcing/TTL
Fast Response	No
Number of Non-Isolated Input Commons	2
Number of Points per Common	8
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v4.2 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/P2-16ND-TTL.pdf>
See store item page for other formats.