

P2-16ND3-1 Cut Sheet



Productivity2000 discrete input module, 16-point, 12-24 VDC, sinking/sourcing, 2 isolated common(s), 8 point(s) per common. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-16ND3-1>

Technical Specifications

Brand	Productivity2000
Item	Input module
I/O Module Type	Discrete
Number of Input Points	16
Nominal Input Voltage	12-24 VDC
Discrete Input Type	Sinking/sourcing
Fast Response	No
Number of Isolated Input Commons	2

Number of Points per Common	8
External Power Requirement	12-24 VDC
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v3.1 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/P2-16ND3-1.pdf>
See store item page for other formats.