


P2-16ND3 Cut Sheet



Productivity2000 discrete input module, 16-point, 12-24 VDC, sinking/sourcing, 1 isolated common(s), 16 point(s) per common. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-16ND3>

Technical Specifications

Brand	Productivity2000
Item	Input module
I/O Module Type	Discrete
Number of Input Points	16
Nominal Input Voltage	12-24 VDC
Discrete Input Type	Sinking/sourcing
Number of Isolated Input Commons	1

Number of Points per Common	16
External Power Requirement	12-24 VDC
For Use With	Productivity2000
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v2.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/P2-16ND3.pdf>
See store item page for other formats.