

P2-16TEP Cut Sheet



Productivity2000 relay output module, 16-point, 24 VAC/VDC, (16) solid state relays, 2 isolated common(s), 8 point(s) per common, 0.5A/point @ 40 °C, 0.3A/point @ 60 °C. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-16TEP>

Technical Specifications

Brand	Productivity2000
Item	Output module
I/O Module Type	Relay
Number of Output Points	16
Nominal Output Voltage	24 VAC/VDC
Relay Configuration	(16) solid state relays
Number of Isolated Commons	2
Jumper Selectable Isolation	No
Number of Points per Common	8

Load Current	0.5A/point @ 40 °C, 0.3A/point @ 60 °C
Protection Type(s)	<ul style="list-style-type: none">• overcurrent• thermal
Fuse Type	User-supplied external fuse
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v4.7 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/P2-16TEP.pdf>
See store item page for other formats.