

# P2-32NE3 Cut Sheet



Productivity2000 discrete input module, 32-point, 24 VAC/VDC, sinking/sourcing, 4 isolated common(s), 8 point(s) per common. Requires ZIPLink connector modules and pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-32NE3>

## Technical Specifications

<b>Brand</b>	Productivity2000
<b>Item</b>	Input module
<b>I/O Module Type</b>	Discrete
<b>Number of Input Points</b>	32
<b>Nominal Input Voltage</b>	24 VAC/VDC
<b>Discrete Input Type</b>	Sinking/sourcing
<b>Fast Response</b>	No
<b>Number of Isolated Input Commons</b>	4

<b>Number of Points per Common</b>	8
<b>For Use With</b>	Productivity2000
<b>Requires</b>	ZIPLink connector modules and pre-wired cables
<b>Programming Software</b>	Productivity Suite programming software v2.1 or later
<b>Additional Information</b>	No terminal block sold for this module

## Agency Approvals

<b>UL Listed File #</b>	E139594
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">ABS Certification Document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/P2-32NE3.pdf>  
See store item page for other formats.