

P2-32NE3 Cut Sheet



Productivity2000 discrete input module, 32-point, 24 VAC/VDC, sinking/sourcing, 4 isolated common(s), 8 point(s) per common. Requires ZIPLink connector modules and pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-32NE3>

Technical Specifications

Brand	Productivity2000
Item	Input module
I/O Module Type	Discrete
Number of Input Points	32
Nominal Input Voltage	24 VAC/VDC
Discrete Input Type	Sinking/sourcing
Fast Response	No
Number of Isolated Input Commons	4
Number of Points per Common	8
For Use With	Productivity2000
Requires	ZIPLink connector modules and pre-wired cables
Programming Software	Productivity Suite programming software v2.1 or later
Additional Information	No terminal block sold for this module

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document