

P2-8AD4DA-1 Cut Sheet



Productivity2000 analog combo module, Input: 8-channel, current, 0-20 mA, Output: 4-channel, current, 4-20 mA. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-8AD4DA-1>

Technical Specifications

Brand	Productivity2000
Item	Combo module
I/O Module Type	Analog
Number of Input Channels	8
Input Signal Type(s)	Current
Analog Input Type	Sinking
Number of Non-Isolated Input Commons	2
Input Resolution	16-bit
Input Current Signal Range	0-20 mA
Number of Output Channels	4
Output Signal Type	Current

Analog Output Type	Sourcing
Number of Non-Isolated Output Commons	2
Output Resolution	16-bit
Output Current Signal Range	4-20 mA
Display Type	4 x 10 character OLED display
External Power Requirement	24 VDC
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v2.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document