

P2-RS Cut Sheet



Productivity2000 remote I/O module, 4 ports, (1) Ethernet (RJ45), (1) RS-232 (RJ12), (1) RS-485 (3-pin terminal) and (1) microB-USB port(s), 4 x 10 character OLED display.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-RS>

Technical Specifications

Brand	Productivity2000
Item	Remote I/O module
Number of Ports	4
Buffered Ports	No
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) Ethernet (RJ45)• (1) RS-232 (RJ12)• (1) RS-485 (3-pin terminal)• (1) microB-USB
Port Protocol(s)	<ul style="list-style-type: none">• Modbus RTU Master/Slave• ASCII In/out• remote I/O• programming and monitoring
Port Speed(s)	<ul style="list-style-type: none">• 10/100 Mbps• up to 115.2k baud
Display Type	4 x 10 character OLED
Programming Software	Productivity Suite programming software v2.2 or later
Additional Information	Installs in the CPU slot of each remote base

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document