

P20 Cut Sheet



PBC Simplicity series single pillow block, plain bearing, 3.63in overall length, PTFE, 1-1/4in inside diameter, aluminum housing, 0.0005in running clearance. For use with 1-1/4in diameter PBC shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P20>

Technical Specifications

| | |
|--------------------------------|-----------------------------|
| Brand | PBC |
| Item | Single pillow block |
| Series | Simplicity |
| Block Type | Closed type |
| Overall Length | 3.63in |
| Bearing Type | Plain bearing |
| Bearing Material | PTFE |
| Housing Fit | Self-aligning |
| Bearing Inside Diameter | 1-1/4in |
| Housing Material | Aluminum |
| Running Clearance | 0.0005in |
| For Use With | 1-1/4in diameter PBC shafts |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/P20.pdf>
See store item page for other formats.