

P21EDBP-22-28 Cut Sheet



Metrol limit switch, tool setter, high precision touch, 41 x 45 x 25mm, 10mm flat head, tungsten carbide, 18.5mm plunger, 1.5N contact force, N.C. contact(s), 16.4ft/5m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P21EDBP-22-28>

Technical Specifications

Brand	Metrol
Item	Limit switch
Application	Tool setter
Switch Type	High precision touch
Housing Size	41 x 45 x 25mm
Head Type	10mm flat
Actuator Type	18.5mm plunger
Contact Force	1.5N
Contact Type	N.C.
Cable Length	16.4ft/5m
Connection	Pigtail
Conductor Size	30 AWG
Stroke	5mm
Repeatability	0.0005mm
Material	Stainless steel
IP Rating	IP67
Operating Temperature	0 to 80 deg C
Indicating Type	LED indication

Agency Approvals

RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/P21EDBP-22-28.pdf>
See store item page for other formats.