


P3-01DC Cut Sheet



Productivity3000 DC base power supply, 24-48 VDC nominal input. (1) power supply required per base.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-01DC>

Technical Specifications

Brand	Productivity3000
Item	Base power supply
Voltage Type	DC
Nominal Input Voltage	24-48 VDC
Programming Software	Productivity Suite programming software v1.2 or later
Additional Information	(1) power supply required per base

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/P3-01DC.pdf>
See store item page for other formats.