

P3-04ADS Cut Sheet



Productivity3000 analog input module, 4-channel, current/voltage, 16-bit, isolated. Requires P3-RTB removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-04ADS>

Technical Specifications

Brand	Productivity3000
Item	Input module
I/O Module Type	Analog
Number Of Input Channels	4
Input Signal Type(s)	Current/voltage
Analog Input Type	Sinking
Number of Isolated Commons	4

Isolated Channels	Yes
Input Resolution	16-bit
Input Current Signal Range	0-20 mA
Input Voltage Signal Range	0-5 VDC, 0-10 VDC, +/- 10 VDC
Display Type	4 x 10 character LCD display
Requires	P3-RTB removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v1.2 or later

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/P3-04ADS.pdf>
See store item page for other formats.