

P3-08TD2S Cut Sheet



Productivity3000 discrete output module, 8-point, 6-24 VDC, sourcing, 4 isolated common(s), 2 point(s) per common, 2A/point, 4A/common. Requires P3-RTB removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-08TD2S>

Technical Specifications

Brand	Productivity3000
Item	Output module
I/O Module Type	Discrete
Number of Output Points	8
Nominal Output Voltage	6-24 VDC
Discrete Output Type	Sourcing
Number of Isolated Output Commons	4
Number of Points per Common	2
Load Current	2A/point, 4A/common
Requires	P3-RTB removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v1.2 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document