

# P3-08THM Cut Sheet



Productivity3000 temperature input module, thermocouple, 8-channel, 16-bit resolution, input thermocouple type(s): J, E, K, R, S, T, B, N, C. (1) P3-RTB screw terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-08THM>

## Technical Specifications

<b>Brand</b>	Productivity3000
<b>Item</b>	Input module
<b>I/O Module Type</b>	Temperature
<b>Input Signal Type(s)</b>	Thermocouple
<b>Number Of Input Channels</b>	8
<b>Input Thermocouple Signal Type</b>	J, E, K, R, S, T, B, N, C
<b>Input Voltage Signal Range</b>	0-1.25 VDC, 0-39.0625 mVDC, +/- 39.0625 mVDC, +/- 78.125 mVDC, 0-156.25 mVDC, +/- 156 mVDC

<b>Input Resolution</b>	16-bit
<b>Display Type</b>	4 x 10 character LCD display
<b>Includes</b>	(1) P3-RTB screw terminal block
<b>Programming Software</b>	Productivity Suite programming software v1.2 or later
<b>Additional Information</b>	Pre-wired ZIPLinks not available for temperature modules

## Agency Approvals

<b>UL Listed File #</b>	E157382
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	E200031
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">ABS Certification Document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/P3-08THM.pdf>  
See store item page for other formats.