

P3-16TA Cut Sheet



Productivity3000 discrete output module, 16-point, 120-240 VAC, 2 isolated common(s), 8 point(s) per common, 0.5A/point, 4A/common. Requires P3-RTB removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-16TA>

Technical Specifications

Brand	Productivity3000
Item	Output module
I/O Module Type	Discrete
Number of Output Points	16
Nominal Output Voltage	120-240 VAC
Number of Isolated Output Commons	2
Number of Points per Common	8
Load Current	0.5A/point, 4A/common
Fuse Type	Replaceable fuse
Requires	P3-RTB removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v1.2 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document