

# P3-16TD3P Cut Sheet



Productivity3000 discrete output module, 16-point, 12-24 VDC, sinking and sourcing, 4 common(s), 4 point(s) per common, 0.5A/point, 4A/common, short circuit and overload protection. Requires ZIPLink connector modules and pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-16TD3P>

## Technical Specifications

Brand	Productivity3000
Item	Output module
I/O Module Type	Discrete
Number of Output Points	16
Nominal Output Voltage	12-24 VDC
Discrete Output Type	Sinking/sourcing
Number of Non-Isolated Output Commons	4
Number of Points per Common	4

Load Current	0.5A/point, 4A/common
Protection Type(s)	<ul style="list-style-type: none"><li>• short circuit</li><li>• overload</li></ul>
External Power Requirement	24 VDC
Requires	ZIPLink connector modules and pre-wired cables
Programming Software	Productivity Suite programming software v1.6 or later
Additional Information	No terminal block sold for this module

## Agency Approvals

UL Listed File #	E157382, E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>
Other	ABS Certification Document

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/P3-16TD3P.pdf>  
See store item page for other formats.