

# P3-8AD4DA-2 Cut Sheet



Productivity3000 analog combo module, Input: 8-channel, voltage, 0-5 VDC and 0-10 VDC, Output: 4-channel, voltage, 0-5 VDC and 0-10 VDC. Requires P3-RTB removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-8AD4DA-2>

## Technical Specifications

<b>Brand</b>	Productivity3000
<b>Item</b>	Combo module
<b>I/O Module Type</b>	Analog
<b>Number of Input Channels</b>	8
<b>Input Signal Type(s)</b>	Voltage
<b>Number of Non-Isolated Input Commons</b>	4
<b>Input Resolution</b>	16-bit
<b>Input Voltage Signal Range</b>	0-5 VDC and 0-10 VDC
<b>Number of Output Channels</b>	4
<b>Output Signal Type</b>	Voltage
<b>Number of Non-Isolated Output Commons</b>	2

<b>Output Resolution</b>	16-bit
<b>Output Voltage Signal Range</b>	0-5 VDC and 0-10 VDC
<b>Display Type</b>	4 x 10 character LCD display
<b>External Power Requirement</b>	24 VDC
<b>Requires</b>	P3-RTB removable terminal block or ZIPLink pre-wired cables
<b>Programming Software</b>	Productivity Suite programming software v1.2 or later
<b>Additional Information</b>	Optional ZIPLink connector modules and pre-wired cables are available

## Agency Approvals

<b>UL Listed File #</b>	E157382
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	E200031
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">ABS Certification Document</a>