

P3-8AD4DA-2 Cut Sheet



Productivity3000 analog combo module, Input: 8-channel, voltage, Output: 4-channel, voltage. Requires P3-RTB removable terminal block or ZIPLink pre-wired cables. Optional ZIPLink connector modules and pre-wired cables are available.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-8AD4DA-2>

Technical Specifications

Brand	Productivity3000
Item	Combo module
I/O Module Type	Analog
Number of Input Channels	8
Input Signal Type(s)	Voltage
Number of Non-Isolated Input Commons	4
Input Resolution	16-bit
Input Voltage Signal Range	0-5 VDC and 0-10 VDC
Number of Output Channels	4
Output Signal Type	Voltage
Number of Non-Isolated Output Commons	2

Output Resolution	16-bit
Output Voltage Signal Range	0-5 VDC and 0-10 VDC
Display Type	4 x 10 character LCD display
External Power Requirement	24 VDC
Requires	P3-RTB removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v1.2 or later
Additional Information	Optional ZIPLink connector modules and pre-wired cables are available

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/P3-8AD4DA-2.pdf>
See store item page for other formats.