


P3-EX Cut Sheet



Productivity3000 local I/O expansion module, 2 ports, (1) USB A and (1) USB B port(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P3-EX>

Technical Specifications

Brand	Productivity3000
Item	Local I/O expansion module
Number of Ports	2
Buffered Ports	No
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) USB A• (1) USB B
Programming Software	Productivity Suite programming software v1.2 or later
Additional Information	Installs in the CPU slot of each expansion base. Connects to the CPU, remote slave or previous expansion unit with the P3-EX-CBL6 USB cable

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document