

P84F-3AT-PFA Cut Sheet



Norgren soft start valve, 3-port (3-way), 2-position, single solenoid spring return, N.C., 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), 1/2in female NPT exhaust(s), Cv=2.9, 24 VDC operating voltage. For use with Excelon Plus 84 series components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P84F-3AT-PFA>

Technical Specifications

Brand	Norgren
Series	Excelon Plus 84
Item	Valve
Working Fluid	Air
Valve Type	Soft start
Action	Single solenoid spring return
Port Quantity	3-port (3-way)
Number Of Positions	2
Valve Configuration	N.C.
Inlet Port	3/8in female NPT
Outlet Port	3/8in female NPT
Exhaust Port	1/2in female NPT
Flow Coefficient	2.9
Operating Voltage	24 VDC
Electrical Connection	8mm DIN style wiring plug
For Use With	Excelon Plus 84 series components
Includes	Field wireable DIN connector

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement