

# P9-4906 Cut Sheet



Trumeter electromechanical counter, 4mm 6-digit analog, 12 VDC input, manual reset, rectangular 2-hole mount, (2) 10in 22 AWG pigtails.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P9-4906>

## Technical Specifications

<b>Brand</b>	Trumeter
<b>Item</b>	Counter
<b>Counter Type</b>	Electromechanical
<b>Count Direction</b>	Up
<b>Count Speed</b>	600 counts/min
<b>Display Type</b>	Analog
<b>Display Size</b>	4mm 6-digit
<b>Reset</b>	Manual
<b>Input</b>	12 VDC
<b>Operating Voltage</b>	12 VDC
<b>Mounting</b>	Panel
<b>Mounting Type</b>	Rectangular 2-hole mount
<b>Mounting Hole Size</b>	2.00 x 1.01in
<b>Connector Type</b>	(2) 10in 22 AWG pigtails

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E36690
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>