

# PAL-ACC05 Cut Sheet



NITRA control cable, 25-pin D-sub right-angle female to pigtail, IP65, 8.2ft/2.5m cable length. For use with PAL-E25 electrical connection module.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PAL-ACC05>

## Technical Specifications

Brand	NITRA
Item	Cable
Cable Type	Control
Replacement	No
Connection 1	25-pin D-sub right-angle female
Connection 2	Pigtail
IP Rating	IP65
Shielded	No
Twisted Pair	No
Cable Length	8.2ft/2.5m
Conductor Size	24 AWG
For Use With	PAL-E25 electrical connection module

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/PAL-ACC05.pdf>  
See store item page for other formats.