

PAL-ACC06 Cut Sheet



NITRA control cable, 25-pin D-sub right-angle female to pigtail, IP65, 16.4ft/5m cable length. For use with PAL-E25 electrical connection module.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PAL-ACC06>

Technical Specifications

Brand	NITRA
Item	Cable
Cable Type	Control
Replacement	No
Connection 1	25-pin D-sub right-angle female
Connection 2	Pigtail
IP Rating	IP65
Shielded	No
Twisted Pair	No
Cable Length	16.4ft/5m
Conductor Size	24 AWG
For Use With	PAL-E25 electrical connection module

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PAL-ACC06.pdf>
See store item page for other formats.