

PAL-P12 Cut Sheet



NITRA pneumatic compressed air module, left supply/exhaust, Cv=3.76, 1/2in push-to-connect inlet(s), silenced exhaust(s), 5/32in (4mm) push-to-connect pilot(s), IP65. For use with PAL series.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PAL-P12>

Technical Specifications

Brand	NITRA
Item	Compressed air module
Working Fluid	Air or inert gas
Pneumatic Function	Left supply/exhaust
Flow Coefficient	3.76
Inlet Port	1/2in push-to-connect
Exhaust Port	Silenced
Pilot Port	5/32in (4mm) push-to-connect
IP Rating	IP65
For Use With	PAL series
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	YIOZ2.MH64380
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PAL-P12.pdf>
See store item page for other formats.