

PAL-S07 Cut Sheet



NITRA discrete output module, 16-point, 12-24 VDC, PNP/NPN, 1 common(s), 16 point(s) per common, 0.5A/point, 3A/common, short circuit and overload protection, IP40. Mounting hardware included. Requires PAL-EIP bus coupler.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PAL-S07>

Technical Specifications

Brand	NITRA
Item	Output module
I/O Module Type	Discrete
Connector Type	Spring clamp terminal
Number of Output Points	16
Nominal Output Voltage	12-24 VDC
Discrete Output Type	PNP/NPN
Number of Non-Isolated Output Commons	1

Number of Points per Common	16
Load Current	0.5A/point, 3A/common
Protection Type(s)	<ul style="list-style-type: none">• short circuit• overload
IP Rating	IP40
Includes	Mounting hardware
Requires	PAL-EIP bus coupler
Programming Software	NITRA PAL configuration software v1.0 or later

Agency Approvals

UL Listed File #	None
UL Recognized File #	YIOZ2.MH64380
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PAL-S07.pdf>
See store item page for other formats.