

PAL-V1-32C Cut Sheet



NITRA solenoid valve, 3-way, 2-position, 1 high-flow N.C., single solenoid spring return, reinforced technopolymer body, IP65, locking manual override, Cv=1.28, 12-24 VDC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PAL-V1-32C>

Technical Specifications

Brand	NITRA
Series	Pneumatic automation link (PAL)
Item	Valve
Working Fluid	Air
Valve Type	Solenoid directional control
Port Quantity	3-way
Number Of Positions	2
Valve Configuration	1 high-flow N.C.
Action	Single solenoid spring return
Body Material	Reinforced technopolymer
IP Rating	IP65
Manual Override Type	Locking
Flow Coefficient	1.28
Operating Voltage	12-24 VDC
Indicating Type	LED indication
Form Factor	Modular
For Use With	PAL series
Includes	Mounting hardware
Requires	PAL series valve base

Agency Approvals

UL Listed File #	None
UL Recognized File #	Y10Z2.MH64380
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document