

PB1012 Cut Sheet



Edison open terminal block, 175A, 2-pole, line side: 1 opening accepts 2/0 AWG to 8 AWG, load side: 1 opening accepts 2/0 AWG to 8 AWG, panel mount, UL 1059 recognized.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PB1012>

Technical Specifications

Brand	Edison
Item	Open Terminal block
Amperage Rating	175A
Number of Poles	2
Line Side Openings	1 opening accepts 2/0 AWG to 8 AWG
Load Side Openings	1 opening accepts 2/0 AWG to 8 AWG
Mounting	Panel
SCCR Rating	200kA SCCR
UL Rating	UL 1059 recognized

Agency Approvals

UL Listed File #	None
UL Recognized File #	E62622
UL Hazardous File #	None
CE	View CE declarations
CSA File #	700489
RoHS Status	No
EU REACH	View EU REACH document
Other	None