

# PB1013 Cut Sheet



Edison open terminal block, 175A, 3-pole, line side: 1 opening accepts 2/0 AWG to 8 AWG, load side: 1 opening accepts 2/0 AWG to 8 AWG, panel mount, UL 1059 recognized.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PB1013>

## Technical Specifications

<b>Brand</b>	Edison
<b>Item</b>	Open Terminal block
<b>Amperage Rating</b>	175A
<b>Number of Poles</b>	3
<b>Line Side Openings</b>	1 opening accepts 2/0 AWG to 8 AWG
<b>Load Side Openings</b>	1 opening accepts 2/0 AWG to 8 AWG
<b>Mounting</b>	Panel
<b>SCCR Rating</b>	200kA SCCR
<b>UL Rating</b>	UL 1059 recognized

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E62622
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	700489
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	None