

PB3BC Cut Sheet



Wiegmann pushbutton enclosure, blank cover, NEMA 4/12/13, 8 x 3 x 3in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PB3BC>

Technical Specifications

| | |
|-------------------------------------|----------------------|
| Brand | Wiegmann |
| Item | Pushbutton enclosure |
| Number of Pushbutton Holes | Blank cover |
| Slope Top | No |
| NEMA Rating | 4/12/13 |
| Nominal Enclosure Dimensions | 8 x 3 x 3in (HxWxD) |
| Enclosure Height | 8.25in |
| Enclosure Width | 3.56in |
| Enclosure Depth | 3.14in |
| Mounting | Wall |

| | |
|---------------------------------|--------------|
| Integral Mounting Feet | No |
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Screw cover |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PB3BC.pdf>
See store item page for other formats.