

PB4012 Cut Sheet



Edison open terminal block, 380A, 2-pole, line side: 1 opening accepts 500 MCM to 6 AWG, load side: 3/8-16 X 1 stud, panel mount, UL 1059 recognized.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PB4012>

Technical Specifications

Brand	Edison
Item	Terminal block
Terminal Block Type	Open
Amperage Rating	380A
Number of Poles	2
Line Side Openings	1 opening accepts 500 MCM to 6 AWG
Load Side Openings	3/8-16 X 1 stud
Mounting	Panel
SCCR Rating	10kA SCCR
UL Rating	UL 1059 recognized

Agency Approvals

UL Listed File #	None
UL Recognized File #	E62622
UL Hazardous File #	None
CE	View CE declarations
CSA File #	700489
RoHS Status	No
EU REACH	View EU REACH document
Other	None

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PB4012.pdf>
See store item page for other formats.