

# PB5122 Cut Sheet



Edison open terminal block, 570A, 2-pole, line side: 2 openings accept 300 MCM to 4 AWG, load side: 12 openings accept 4AWG to 14 AWG, panel mount, UL 1059 recognized.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PB5122>

## Technical Specifications

Brand	Edison
Item	Terminal block
Terminal Block Type	Open
Amperage Rating	570A
Number of Poles	2
Line Side Openings	2 openings accept 300 MCM to 4 AWG
Load Side Openings	12 openings accept 4AWG to 14 AWG
Mounting	Panel
SCCR Rating	10kA SCCR
UL Rating	UL 1059 recognized

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E62622
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	700489
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>
Other	None

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/PB5122.pdf>  
See store item page for other formats.