


PBFS19015GY2 Cut Sheet



Hammond rack panel, 9U, 19in rack width, flanged, carbon steel, ANSI 61 gray, powder coat finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PBFS19015GY2>

Technical Specifications

| | |
|--------------------|--------------|
| Brand | Hammond |
| Item | Rack panel |
| Rack Height | 9U |
| Rack Width | 19in |
| Height | 15.75in |
| Flanged | Yes |
| Knockouts | No |
| Perforated | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PBFS19015GY2.pdf>
See store item page for other formats.