

PBFS19017GY2 Cut Sheet



Hammond rack panel, 10U, 19in rack width, flanged, carbon steel, ANSI 61 gray, powder coat finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PBFS19017GY2>

Technical Specifications

Brand	Hammond
Item	Rack panel
Rack Height	10U
Rack Width	19in
Height	17.5in
Flanged	Yes
Knockouts	No
Perforated	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PBFS19017GY2.pdf>
See store item page for other formats.