

PBGX3SSA Cut Sheet



Wiegmann pushbutton enclosure, 3 holes, 22mm, NEMA 4/4X/12/13, 7 x 3 x 4in (HxWxD), wall mount, 316 stainless steel, No. 3 intermediate polished finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PBGX3SSA>

Technical Specifications

Brand	Wiegmann
Item	Pushbutton enclosure
Number of Pushbutton Holes	3 holes
Pushbutton Hole Nominal Size	22mm
Slope Top	No
NEMA Rating	4/4X/12/13
Nominal Enclosure Dimensions	7 x 3 x 4in (HxWxD)
Enclosure Height	7.31in
Enclosure Width	3.06in

Enclosure Depth	3.83in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	316 stainless steel
Finish	No. 3 intermediate polished
Cover Type	Screw cover
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	No
EU REACH	View EU REACH document