


PBPA19017GY2 Cut Sheet



Hammond rack panel, 10U, 19in rack width, 5052-H32 aluminum, ANSI 61 gray, powder coat finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PBPA19017GY2>

Technical Specifications

Brand	Hammond
Item	Rack panel
Rack Height	10U
Rack Width	19in
Height	17.5in
Flanged	No
Knockouts	No
Perforated	No
Material	5052-H32 aluminum
Color	ANSI 61 gray
Finish	Powder coat

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PBPA19017GY2.pdf>
See store item page for other formats.