


PBSS12A Cut Sheet



Wiegmann pushbutton enclosure, 12 holes, 30mm, NEMA 4/4X/12/13, 12 x 9 x 3in (HxWxD), wall mount, 316L stainless steel, No. 3 intermediate polished finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PBSS12A>

Technical Specifications

Brand	Wiegmann
Item	Pushbutton enclosure
Number of Pushbutton Holes	12 holes
Pushbutton Hole Nominal Size	30mm
NEMA Rating	4/4X/12/13
Nominal Enclosure Dimensions	12 x 9 x 3in (HxWxD)
Enclosure Height	12.00in
Enclosure Width	8.81in
Enclosure Depth	3.29in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	Yes
Knockouts	No
Material	316L stainless steel
Finish	No. 3 intermediate polished
Cover Type	Screw cover

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document