

PBYX36 Cut Sheet



Wiegmann pushbutton enclosure, 36 holes, 30mm, NEMA 12/13, 19 x 18 x 6in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, hinged screw cover, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PBYX36>

Technical Specifications

Brand	Wiegmann
Item	Pushbutton enclosure
Number of Pushbutton Holes	36 holes
Pushbutton Hole Nominal Size	30mm
Slope Top	No
NEMA Rating	12/13
Nominal Enclosure Dimensions	19 x 18 x 6in (HxWxD)
Enclosure Height	18.82in
Enclosure Width	17.88in
Enclosure Depth	6.33in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Hinged screw cover
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Padlockable	No
Keylocking	No
Subpanel	Subpanel included

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document