

PBYX9 Cut Sheet



Wiegmann pushbutton enclosure, 9 holes, 30mm, NEMA 12/13, 11 x 10 x 6in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, hinged screw cover, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PBYX9>

Technical Specifications

| | |
|-------------------------------------|-----------------------|
| Brand | Wiegmann |
| Item | Pushbutton enclosure |
| Number of Pushbutton Holes | 9 holes |
| Pushbutton Hole Nominal Size | 30mm |
| Slope Top | No |
| NEMA Rating | 12/13 |
| Nominal Enclosure Dimensions | 11 x 10 x 6in (HxWxD) |
| Enclosure Height | 11.32in |
| Enclosure Width | 10.38in |
| Enclosure Depth | 6.33in |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|----------------------------------|--------------------|
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Hinged screw cover |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Padlockable | No |
| Keylocking | No |
| Subpanel | Subpanel included |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |