

PD05PD5CY Cut Sheet



Lumher PD machine vision lighting, bar light, white light emission, 5000K, plus or minus 30 degrees, 450mm luminous field, continuous, 494 x 31 x 25mm housing, 22.8-25.2 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PD05PD5CY>

Technical Specifications

Brand	Lumher
Series	PD
Item	Machine vision lighting
Light Type	Bar light
Light Emission	White
Color Temperature	5000K
Beam Angle	Plus or minus 30 degrees
Luminous Field	450mm
Housing Size	494 x 31 x 25mm

Body Material	Anodized aluminum
Operation Mode	Continuous
Overdrive	No
Operating Voltage	22.8-25.2 VDC
Power Rating	9.5W
Current Consumption Continuous	0.4A
IP Rating	IP65
Connection	4-pin M12 quick-disconnect

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PD05PD5CY.pdf>
See store item page for other formats.