

PE12NAT500 Cut Sheet



HydroMode potable water tubing, polyethylene, natural, 1/2in outside diameter, 3/8in inside diameter, 500ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE12NAT500>

Technical Specifications

Brand	HydroMode
Item	Tubing
Working Fluid	Potable water
Material	Polyethylene
Color	Natural
Outside Diameter	1/2in
Inside Diameter	3/8in
UV stabilized	No
Working Length	500ft reel
Operating Pressure	75 psi
Operating Temperature	-50 to +140 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document