


# PE12WHT500 Cut Sheet



HydroMode potable water tubing, polyethylene, white, 1/2in outside diameter, 3/8in inside diameter, NSF/ANSI 61, 500ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE12WHT500>

---

## Technical Specifications

<b>Brand</b>	HydroMode
<b>Item</b>	Tubing
<b>Working Fluid</b>	Potable water
<b>Material</b>	Polyethylene
<b>Color</b>	White
<b>Outside Diameter</b>	1/2in
<b>Inside Diameter</b>	3/8in
<b>Potable Water Certifications</b>	NSF/ANSI 61
<b>UV stabilized</b>	No
<b>Working Length</b>	500ft reel
<b>Operating Pressure</b>	75 psi
<b>Operating Temperature</b>	-50 to +140 deg F

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>