

PE14NAT1000 Cut Sheet



HydroMode potable water tubing, polyethylene, natural, 1/4in outside diameter, 0.170in inside diameter, NSF/ANSI 61, 1000ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE14NAT1000>

Technical Specifications

Brand	HydroMode
Item	Potable water Tubing
Material	Polyethylene
Color	Natural
Outside Diameter	1/4in
Inside Diameter	0.170in
Agency Approval	NSF/ANSI 61
UV stabilized	No
Working Length	1000ft reel
Operating Pressure	75 psi
Operating Temperature	-50 to +140 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document