

# PE14YEL1000 Cut Sheet



HydroMode potable water tubing, polyethylene, yellow, 1/4in outside diameter, 0.170in inside diameter, NSF/ANSI 61, 1000ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE14YEL1000>

## Technical Specifications

<b>Brand</b>	HydroMode
<b>Item</b>	Potable water Tubing
<b>Material</b>	Polyethylene
<b>Color</b>	Yellow
<b>Outside Diameter</b>	1/4in
<b>Inside Diameter</b>	0.170in
<b>Agency Approval</b>	NSF/ANSI 61
<b>UV stabilized</b>	No
<b>Working Length</b>	1000ft reel
<b>Operating Pressure</b>	75 psi
<b>Operating Temperature</b>	-50 to +140 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>