

# PE38BLU1000 Cut Sheet



HydroMode potable water tubing, polyethylene, blue, 3/8in outside diameter, 1/4in inside diameter, NSF/ANSI 61, 1000ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE38BLU1000>

---

## Technical Specifications

|                              |                      |
|------------------------------|----------------------|
| <b>Brand</b>                 | HydroMode            |
| <b>Item</b>                  | Potable water Tubing |
| <b>Material</b>              | Polyethylene         |
| <b>Color</b>                 | Blue                 |
| <b>Outside Diameter</b>      | 3/8in                |
| <b>Inside Diameter</b>       | 1/4in                |
| <b>Agency Approval</b>       | NSF/ANSI 61          |
| <b>UV stabilized</b>         | No                   |
| <b>Working Length</b>        | 1000ft reel          |
| <b>Operating Pressure</b>    | 75 psi               |
| <b>Operating Temperature</b> | -50 to +140 deg F    |

---

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |